

SPECIFICATIONS

Model	MicroMAS (MicroMAS-D/MicroMAS-H)	2U MAS						
Capacities	Up to 8 ports assigned as either 8 voice mail ports, 8 ACD ports, or a combination of voice mail ports and ACD ports. Voice Mail message storage up to 5,000 hours.	Up to 32 HMP ports assigned as 32 voice mail ports or 32 ACD ports, or up to 16 voice mail ports and up to 16 ACD ports. Voice Mail message storage up to 5,000 hours.						
Measurements <i>Metric</i> <i>English</i>	Width 309 mm 12.2 in.	Height 84 mm 3.3 in.	Depth 325 mm 12.8 in.	Weight 6.81 kg 15 lbs.	Width 440 mm 17.3 in.	Height 88 mm 3.5 in.	Depth 609 mm 24 in.	Weight 15.9 kg 35 lbs.
Power Supply Unit (PSU)	Initially Built-in	Initially Built-in						
Primary AC Power	Standard configured: 115VAC, at 6 amps, 50Hz -60Hz. Switch configured: 230VAC at 3.5 amps, 50Hz -60Hz.	Input AC 120VAC, 5.67 amps max. 400 watts per cabinet. AC Freq. Single-phase amps, (50Hz - 60Hz).						
Power Backup	An Uninterruptible Power Supply (UPS) is required for power backup similar to the ones used for computer systems and networking equipment.							
Cooling	One chassis fan, one CPU fan	Two rear fans, one power supply fan, one CPU fan						
Operating Temperature	32°F ~104°F (0°C ~40°C)	32°F ~122°F (-1.7°C ~50°C)						
Operating Humidity	10%~95% non-condensing	-5%~95% non-condensing						
Storage Temperature	-40°F~140°F (-40°C~60°C)	-40°F ~158°F (-40°C ~70°C)						
Chassis Installation	Table-mount	19" Rack-mount (2U height)						
Compliance	UL E199948	Safety: UL/CSA 60950-1:2003 (UL RecognitionMark). EMI Verification: Verified to FCC, Class A.						
Data Storage Media	80GB Serial ATA Hard disk drive	80GB Serial ATA Hard disk drive						
CD Drive	CD-R\RW	Slimline DVD-RW						
PCI Slots	Two half length	Two full length						
USB Ports	Two – rear connection	Three – front side connection						
Serial I/O Ports	Two – rear connection	Two – front side connection						
CPU	2.93 GHZ Celeron D	2.4 GHZ Pentium 4						
Memory	Standard 512 MB (MicroMAS-D)/1 GB (MicroMAS-H)	1 GB standard (2 GB maximum)						
Operating System	Microsoft Windows XP Professional	Microsoft Windows XP Professional, Windows Server 2003 (Optional)						
Voice Resources	MicroMAS-H Host-based Media Processing (HMP Ver. 3.0), or MicroMAS-D Dialogic boards (D4PC1U).	Host-based Media Processing (HMP Standard Ver. 3.0)						
Connection to Strata CIX	HMP Single Ethernet IP connection through a network switch, or connection through analog voice ports.	HMP Single Ethernet IP connection through a network switch.						
Network Interface	10/100BaseT Ethernet Connection	1x1000/100/10Mbit, 1x100/10Mbit						
Modem	Optional USB modem supported for remote administration							
Remote Access	Remote access via the network using the Windows® XP Remote Desktop feature.							
Standard Applications	Strategy® ES Voice Mail with Auto Attendant, Token Programming, and 5-seat Unified Messaging. Network eManager browser-based system administration. eMonitor monitoring of alarm conditions from multiple Strata CIX systems. My Phone Manager browser-based personal administration.							
Optional Applications	Additional Strategy ES ports. Strategy ES feature groups additional Unified Messaging seats, Fax, Automated Speech Recognition, Text-to-Speech. Interactive Voice Response capabilities available via Token Programming or custom development. Strata Automatic Call Distribution (ACD) and SYS modules. Insight or TASKE ACD Reporting. Strata Call Manager, Web-based telephone applications. FeatureFlex adaptability/customization tools.							
Application Installation	All application software is pre-installed. Optional applications and Strategy ES feature groups activated through license control. IVR capabilities deployed by Authorized Toshiba Dealers.							
Optional Hardware	Dual redundant power supplies, redundant array of independent drives (RAID*) - levels 1 and 5. *RAID option systems are only sold as turn-key solutions.							

TOSHIBA
Leading Innovation >>>



Toshiba America Information Systems, Inc.
Telecommunication Systems Division

9740 Irvine Blvd., Irvine, CA 92618-1697
To locate an Authorized Dealer, call: (800) 222-5805
National Accounts (800) 234-4873
www.telecom.toshiba.com

© 2011 Toshiba America Information Systems, Inc. All product, service and company names are trademarks, registered trademarks or service marks of their respective owners. Information including without limitation specifications, availability, content of services, and contact information is subject to change without notice.

Literature Order #: TSD-CIX-BR-MAS-DS-VG/4500133